

## BELCON 275 DEPOSITOR

Perfect for conveyor

Beldos offers a range of versatile volumetric stainless steel depositors with optional attachments for depositing, injection, layering and decoration. Beldos depositors will replace your pastry bag, spoon or a measuring cup and will become the most reliable, easy-to-use and intelligent equipment at your production!

### 1. The Belcon depositor is available in three series:

- 275 – 5-275 ml per deposit;
- 670 – 5-670 ml per deposit;
- 1340 - 5-1340 ml per deposit;

### 2. Design features:


- designed for production lines;
- mounted on a mobile heavy duty frame manually adjustable in height;
- height adjustment feet for horizontal leveling at the conveyor;
- optional locating bracket for blocking the depositor always on the right position at the conveyor belt;
- 60 l hopper;
- the depositing volume is indicated on a scale from 10% till 100% depending on the product cylinder volume;
- the speed of depositing can be easily adjustable;
- foot pedal operation or handgun operation or automatic sensor operation on the conveyor; press the foot pedal or the trigger of the handgun once for single portion control or hold for multiple deposits;

### 3. Technical specifications

Depositing speed	Up to 120 deposits/min
Power	Air: 29 l/min at 30 deposits/min 7 Bar / 102 PSI
Depositing volume	5-275 cm <sup>3</sup>
Material	Stainless steel



### 4. Dimensions




























Beldos N.V., Kruiningenstraat 93/95, B-2900, Schoten, Antwerp province, Belgium

Phone: +32 3 646 40 48 Fax: +32 3 646 42 46






www.beldos.com Email: [info@beldos.be](mailto:info@beldos.be)



Publisher: Beldos N.V. Without permission of the publisher nothing from this folder can be copied. © 01.01.2017

5. Options																					
<p>Locating bracket for the right position at the conveyor belt</p> 	<p>Balancer for handgun nozzles</p> 	<p>Height adjustable table</p> 	<p>Guide systems for round/rectangular forms</p> 	<p>Product cylinder+piston, for different deposit volumes</p> 																	
<p>Product cylinder size chart</p> <table border="1" data-bbox="193 831 636 1061"> <thead> <tr> <th rowspan="2">Cylinder size, Ø, mm</th> <th colspan="2">Deposit volume (cm<sup>3</sup>)</th> </tr> <tr> <th>min</th> <th>max</th> </tr> </thead> <tbody> <tr> <td>28</td> <td>5</td> <td>40</td> </tr> <tr> <td>40</td> <td>10</td> <td>86</td> </tr> <tr> <td>52</td> <td>30</td> <td>151</td> </tr> <tr> <td>70</td> <td>100</td> <td>275</td> </tr> </tbody> </table>		Cylinder size, Ø, mm	Deposit volume (cm <sup>3</sup> )		min	max	28	5	40	40	10	86	52	30	151	70	100	275	<p>Rotation cylinders, for different product temperatures</p> 	<p>Conical hoppers, 25/60 l, for flowable products</p> 	<p>Vertical hoppers 25/60 l, for heavy products</p> 
Cylinder size, Ø, mm	Deposit volume (cm <sup>3</sup> )																				
	min	max																			
28	5	40																			
40	10	86																			
52	30	151																			
70	100	275																			
<p>Heating jackets, till +120°C</p> 	<p>Follower plates, synthetic, for heavy and aerated products</p> 	<p>Follower plates, stainless steel, to use on follower plate synthetic; for very heavy products</p> 	<p>Hopper division; removable; to deposit two different flavors from one nozzle outlet (marble cake, etc.)</p> 	<p>Stirrer single system, to mix well products</p> 																	
<p>Extension tubes for nozzles</p> 	<p>Nozzle 90°, for soft, heavy paste, aerated products</p> 	<p>Handgun nozzle, for liquid, semi-liquid products, soft paste, heavy paste, aerated products</p> 	<p>Horizontal nozzle, for soft paste, heavy paste, aerated products</p> 	<p>Rotary cut-off nozzle, for semi-liquid products, soft paste, heavy paste, aerated products</p> 																	

<p>Injection nozzle double, for semi-liquid products, soft paste, aerated products</p>  	<p>Vertical nozzle, for liquid, semi-liquid products, soft paste, heavy paste, aerated products</p>  	<p>Diving nozzle ECONO, for soft paste, heavy paste, aerated products</p>  	<p>Diving nozzle, for soft paste, heavy paste, aerated products</p>  	<p>Sheet icing nozzle, for semi-liquid products, soft paste, heavy paste, aerated products</p>  
<p>Multi 2/3/4 system (automatic multi dosing system)</p>  	<p>Double injection/fill attachment, to attach injection needles/pastry tips/tubes</p>  	<p>Filling tube attachment</p>  	<p>Injection needle attachment</p>  	<p>Spreader &amp; icing attachments, straight or 45°</p>  
<p>Pastry tips 9 pcs; to attach to Beldos nozzles with thread;</p> 	<p>Cream cover head attachments, star &amp; plain tips</p>  		<p>Twisted rosettes head attachments</p>  	



<p>Foot pedal, press once for single portion control or hold for multiple deposits</p> 	<p>Manual switch with spring, to use instead of the foot pedal</p> 	<p>Automatic countdown system, system will automatically count down the number of deposits</p> 	<p>Continuous dosing system, the depositor will run automatically</p> 	<p>Sensor, to activate depositor automatically</p> 
--------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------

<p>Compressors</p> 	<p>Conveyor solutions on request</p> 		
-------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------	--	--

**6. Common applications with additional options:**

- liquid/semi-liquid products, soft & heavy paste, aerated products;
- anything that can be squeezed through a pastry bag;
- with or without particles (nuts, raisins, pieces of fruit); particle size: max Ø 2,5 cm;

**a. Single depositing (1 nozzle, semi-automatic or automatic on conveyor)**



fruit filling



muffins



sponge cake



mayonnaise



ready meals

**b. Multi depositing (2-4 nozzles, automatic on conveyor)**



apple filling



mini-cakes



muffins

**c. Injection (semi-automatic)**



berliners



éclairs



profiteroles



horns with  
cheese sauce




eclairs

**d. Single layering (semi-automatic or automatic on conveyor)**



custard



sponge



sandwiches

**e. Multi layering (semi-automatic or automatic on conveyor)**



mousse dessert



mousse dessert



tiramisu



lasagna

**f. Icing of cakes and flans (round/rectangular/square)**



mid layer icing

**g. Decoration (according to your needs)**



cake border



rosettes



stars